

Leica Objective	Cat No.	Working distance	Microscope
HC PL APO 10x/0.40 CS2	506424	2.56mm	HCF2 / HCF3 / CF6 / LS1
HC PL APO 20x/0.75 CS2	506517	0.62mm	HCF2 / HCF3 / CF6 / LS1
HC PL APO 40x/1.30 OIL CS2	506358	0.24mm	HCF2 / HCF3 / CF6 / LS1 (request)
HC PL APO 63x/1.40 OIL CS2	506350	0.14mm	HCF2 / CF6 / LS1 (request)
HC PL APO 63x/1.20 W CORR CS2	506346	0.3mm	HCF2 / LS1
HC PL APO 63x/1.20 W motCORR CS2	506361	0.3mm	HCF3
HC PL APO 86x/1.20 W motCORR STED white	506333	0.3mm	HCF3
HC PL APO 100x/1.40 OIL STED WHITE	506378	0.13	HCF3
HC PL APO 40x/1.10 W CORR CS2	506357	0.65	CF6
L 1,6x/0.05 DLS (DLS illumination)	506409	8.1	LS1 (request)
HC PL FLUOTAR 2,5x/0.07 (DLS illumination)	506523	9.4	LS1
HC PL FLUOTAR 4x/0.13 (DLS illumination)	506412	17	LS1
HC PL FLUOTAR 5x/0.15 IMM DLS (DLS detection)	506534	4.8	LS1
HC APO L 10x/0.30 W DLS (DLS detection)	506524	3.6	LS1
HC APO L 20x/0.50 W DLS (DLS detection)	506421	3.5	LS1
HC FLUOTAR L 25x/0.95 W DLS (detection)	506399	2.5	LS1